

Ideal for frequent material changes the PDII dryer will eliminate downtime and maximize uptime!

System features

- Automatic shut off valves (inlet/outlet) isolate hoppers not in use or while being cleaned
- Easy to use touch screen display for setting different drying temperatures for each hopper
- Temperature set back (optional) prevents over drying by lowering drying temperatures when usage slows or stops
- Service two presses/extruders with our dual closed loop loader option
- Mobile Ready! Dri-Touch controllers interface with Dri-Link mobile App. Available for IOS and Android



Loading Options

- Dri-Air closed loop loading eliminates moisture contamination with ambient plant air. Loader includes: brushless motor, controls and DS receiver
- DAC Compressed air loaders offer a quiet, easy to use loader that uses your shop air to convey material

DRI-AIR
Industries, Inc.
www.dri-air.com
Call us at **860.627.5110**

4-Bed Dual Hopper Portable Dryers

1 dryer, 2 hoppers = fast changeovers and no downtime!

The H-PDII systems provide maximum flexibility.



H-PDII with 60 pound hoppers

Hopper Sizes	Dimensions	
	[l/w/h] inch	[l/w/h] cm
5, 15 & 30-lb	30/52/59 inch	76/132/150 cm
60, 100 & 150-lb	35/63/82 inch	89/160/208 cm
200 & 300-lb	35/67/82 inch	89/170/208 cm

- Drying and processing from one hopper while pre-drying in the other hopper for on the fly changeovers, eliminates downtime
- Material changes are fast and easy by moving the material line from one hopper to the other
- Reduce valuable floor space, eliminate the need for a second dryer by positioning the dryer between two presses/extruder – ideal for two shot injection molders



H-PDII with 15 & 5 pound hoppers

Touch Screen Control

- Our easy to use Dri-Touch 7" color touch screen is standard with HPDII dryers. The Dri-Touch controller provides easy setting of hopper temperatures and includes -49°F dewpoint monitor, 7 day timer, diagnostic functions and easy to navigate screens for loading settings and alarm functions. Plus prevent over drying with temperature set back!

